

## Need an actuator fast?

**Fixed stroke RSA32ST rod style industrial actuators with inline mounts (LMI) available in one week!**

- Ideal for hydraulic and pneumatic replacement
- Can be used for a variety of general motion control applications that include pressing, lifting, pulling or positioning



Quick Ship Actuators				
Configuration String	Part Number	Stroke Length	Max Thrust	Speed
RSA32 BN02 SK6.000 LMI ST1	1132-0864	6"	534 lbf (2375 N)	34 in/sec (850 mm/sec)
RSA32 BN02 SK12.000 LMI ST1	1132-0865	12"	534 lbf (2375 N)	34 in/sec (850 mm/sec)
RSA32 BN05 SK6.000 LMI ST1	1132-0866	6"	1357 lbf (6036 N)	13 in/sec (330 mm/sec)
RSA32 BN05 SK12.000 LMI ST1	1132-0867	12"	1357 lbf (6036 N)	13 in/sec (330 mm/sec)

- Motor mounts ordered as a separate line item
- Accessories like switches and rod ends purchased as separate line items
- Contact your Tolomatic sales team with questions and to check availability
- For full specifications: [RSA Catalog](#)
- For ordering from our full line of stroke configurable actuators, please visit [www.tolomatic.com](http://www.tolomatic.com)

## Online engineering tools to support from design to production

Engineering Tools on [www.tolomatic.com](http://www.tolomatic.com)



EDUCATIONAL  
RESOURCES



CONTACT AN  
ENGINEER



ACTUATOR  
SIZING



3D  
CAD  
LIBRARY



YOUR MOTOR  
HERE®