


BC3 Features



- 3 Frame sizes with loads up to 4,000 lbf (1,814 kg)
- Internal recirculating ball bearing system for high load carrying and bending moment capacities
- Stroke lengths up 205 inches (5,207 mm)
- Low breakaway pressure and smooth operation
- Dual carrier option increases load carrying and bending moment capacities
- Cost-effective alternative to auxiliary rail systems
- US dimensions (standard) and metric (optional) construction