

MXB-P Features



- 6 frame sizes with loads up to 1,292 lb (5,745N)
- Profiled rail with recirculating ball bearings for high load and bending moment capacities
- Belt driven with speeds up to 150 in/sec (3.8 m/s)
- Polyurethane belt with steel members resists stretching
- Stroke lengths up to 200in (5m)
- Large carrier mounting pattern for more load stability and mounting flexibility
- Dual carrier option to increase bending moment capacity
- Your Motor Here® compatible