

MXP-N Features



- 6 Frame sizes with loads up to 370lb (164 kg)
- Internal bearing system intended for applications with external guidance/bearing system
- Configurable Stroke lengths up to 206 in (5,232 mm)
- Offers a space-saving design over typical rod type air cylinders
- Lowest breakaway pressure of the MXP line of cylinders
- Permanently lubricated internal bearing for reduced maintenance