

Power Block 2 Features



- 4 bore sizes from 15.9 to 50.8 mm (0.63 to 2 in)
- Force output up to 1244 lbs (5.5 kN)
- Stroke lengths up to 6 inches (154.2 mm)
- Choice of linear ball or composite bearings
- Four bore sizes for a wide range of force output capabilities
- Ideal for a variety of pick-and-place and material handling applications
- Two different bearing options or increased load carrying flexibility over the standard PB