

DIGITAL I/O

- 24 VDC Digital I/O control for flexible easy operating modes
- Opto-isolated

INPUT SUPPLY

- 10 VDC to 60 VDC
- Logic & Drive Power

M12 CONNECTORS

Industry standard connectors

QUALITY TESTED

- Each ACSI is performance tested at Tolomatic before shipping
- Mounted, configured and tested on Tolomatic electric actuators

ANALOG IN/OUT

- 0-10VDC or
- 4-20mA

DUAL ETHERNET PORTS

Supports Star, Daisy Chain and Ring Topologies




- AOP: Add on profile
- AOI: Add on Instructions
- DLR: Device Level Ring

MODBUS TCP



USB CONFIGURATION PORT



VIBRATION & SHOCK TESTED

- 2 brms, 5-500 Hz, 2 G, 3-axis, 1 hr
- 20 bpeak, half sine, 11 ms, 3-axis

NEMA 23 & NEMA 34

Industry standard NEMA frame sizes

IP65

Protected against dust and low pressure water jets, limited ingress

