

EFFICIENT INTEGRATED MOTOR DESIGN

- Skewed winding minimizes cogging torque for smooth, repeatable motion
- Low electric time constant motor for quick response
- Power dense



STAINLESS STEEL DESIGN

- 316 Stainless steel construction
- Superior corrosion resistance

GREASE PORT

- Integrated into rod end for hygienic design
- Screw re-lubrication system via needle zerk extends screw service life

WELDED JOINTS

Welded, polished joints create the most hygienic seam

BLUE GASKETS & O-RINGS

- Chemically inert
- Wear resistant
- FDA approved

FLEXIBLE FEEDBACK & CABLE OPTIONS



Single (DSL) and dual cable options

FIELD REPLACEABLE SEAL CARTRIDGE

- IP69K rated, wash-down protection
- Clean-in-place compatible
- FDA approved seal cartridge option

MULTIPLE SCREW TECHNOLOGIES

- Ball screws provide efficient motion at an economical price
- Roller screws provide the highest force and longest life



ADDITIONAL OPTIONS

- Brake
- Externally threaded rod end
- Front flange mount
- Rear clevis mount
- Hygienic fasteners
- FDA approved seal cartridge

