

INTERNAL BUMPER

Made of urethane composite to prolong cylinder life and reduce noise



DURABLE DESIGN

Tough, lightweight extruded aluminum in a low profile package

DOVETAIL SLOTS

For easy switch mounting

NICKEL-PLATED SHAFTS

Shafts up to 0.625" diameter

MOUNTING FLEXIBILITY

Threaded holes for base or side mounting



PLATED STEEL TOOLING PLATE

Threaded bolt thru holes for tooling plate mounting

DURABLE BEARING

COMPOSITE BEARINGS

- Thin profile allows use of oversize guide rods
- Best choice for impact use or high contaminant environments



OPTIONS



STOP COLLAR / BUMPER KIT

- Includes 2 stop collars and 1/4" thick polyurethane external bumpers to help absorb impact shock



DUAL TOOLING PLATE

- Added flexibility for many applications



SWITCHES

- Available in Reed, Hall-effect and Triac
- 15ft. cable with flying leads; available with quick-disconnect couplers