

SERVOPLACE™ LZT PRECISION NUT PLACEMENT

● INTEGRATED SERVO MOTOR/ DRIVE/CONTROLLER ●

- IP65 ingress protection
- M12 connectors
- Dual Ethernet ports



● FLEXIBLE CONTROL FOR ANY PLC ●

- Ethernet: EtherNet/IP, Profinet, Modbus TCP, EtherCAT
- Pneumatic Logic with discrete I/O

● SPEEDS UP TO 6 M/S (200 IN/SEC) ●

● STEEL THRUST ROD ●

- Case hardened steel thrust rod for high rigidity and corrosion resistance
- 9.5 mm (3/8") & 12.7 mm (1/2") rod diameters for various nuts
- Internal female threads allow flexible mounting for any tooling

