


B3S Features



- 3 frame sizes with loads up to 8032 lbf (35.7 kN)
- Internal recirculating ball bearing system for high load and bending moment capacities
- Stroke lengths up 179 inches (4,547 mm)
- Ball and acme screw options
- Dual carrier option to increase bending moment capacity
- Your Motor Here® compatible
- US dimensions (standard) and metric (optional) construction