

ACS Stepper Features



- Stepper motor & drive package (NEMA11/17/23/34) with output torques up to 53 in-lbs (6 N-m)
- Smart Actuation: Mounted, configured, pre-tuned and tested with Tolomatic electric actuators
- Digital I/O, Analog I/O or Ethernet operation
- Industrial Ethernet protocol options: EtherNet/IP, Modbus TCP
- Dual Ethernet ports supports star, daisy chain and ring topologies
- 10Vdc to 60Vdc input supply
- ODVA conformant and Plugfest certified EtherNet/IP
- Add On Profiles (AOP) and Add On Instruction (AOI) compatibility for seamless integration with Rockwell PLCs
- Options include cables, planetary gearboxes in 3:1, 5:1, & 10:1 ratios, and 48Vdc power supplies