

ACSI Features



- Integrated servo motor (NEMA23/34) with output torques up to 29 in-lbs (3.28 N-m)
- Smart Actuation: Mounted, configured, pre-tuned and tested with Tolomatic electric actuators
- Digital I/O, Analog I/O or Ethernet operation
- Industrial Ethernet protocol options: EtherNet/IP, PROFINET, Modbus TCP, EtherCAT
- Dual Ethernet ports supports star, daisy chain and ring topologies
- IP65 rating
- M12 connectors
- 10Vdc to 60Vdc input supply
- ODVA conformant and Plugfest certified EtherNet/IP
- Add On Profiles (AOP) and Add On Instruction (AOI) compatibility for seamless integration with Rockwell PLCs
- Options include cables, planetary gearboxes in 3:1, 5:1, & 10:1 ratios, and 48Vdc power supplies