

BC2 Features



- 6 frame sizes with loads up to 400 lb (181 kg)
- Solid bearing for moderate load carrying and guidance requires no lubrication and is field replaceable
- Non-magnetic sealing design does not attract metal particulates making the BC2 a good choice for welding powder metal pressing or metal grinding applications
- Configurable stroke lengths up to 350in (8,890 mm)
- US dimensions (standard) and metric (optional) construction
- Auxiliary carrier option increases load carrying and bending moment capacities
- Adjustable cushions for smooth deceleration
- Adjustable load carrying bracket provides true tracking and load support