

IMA-S Features



- 2 frame sizes, hygienic design for food and beverage applications
- 316 stainless steel construction
- IP69k ingress protection (static)
- EHEDG fastener option
- FDA approved option for seals and O-rings
- Forces up to 11 kN (2,500 lbf)
- Connector and feedback options to match most servo drives
- Skewed winding provides superior force repeatability
- Low electrical time constant motors allows high frequency moves with increased dynamic performance
- Easy-to-use re-lubrication port maximizes service life