

DOUBLE PURCHASE CABLE CYLINDER

TOLOMATIC... THE RODLESS
CYLINDER LEADER

- Doubles the velocity and stroke capacity of cable cylinder without increasing space requirements
- Isolates cylinder from harsh environments

ENDURANCE TECHNOLOGYSM


Endurance Technology features are designed for maximum durability to provide extended service life.

LOCATE REMOTELY

- Cylinder can be located away from work area. Useful in harsh environments and if space/weight are limited

HIGH STRENGTH TUBE

- High-strength, lightweight, black anodized aluminum or steel
- Creates chamber for pneumatic or hydraulic pressure and protects piston



DIE CAST HEAD ASSEMBLY

- High-strength, lightweight anodized aluminum
- Protects piston and creates chamber for pneumatic or hydraulic pressure

UNIQUE GLAND SEALS

- Tight seal for cables to pass through
- Easy installation
- Snap In/Out cable seals or encapsulated gland seals depending on bore size



ALUMINUM PISTON

- High-strength, lightweight aluminum
- Pulls the cables when actuated by pneumatic or hydraulic pressure



PORTING CHOICES

- Choose from 2 or 3 port heads



OPTIONS



AUTO TENSIONER

- Maintains proper cable tension
- Maximizes service life of both cable and seals



CALIPER DISC BRAKE **HM HN**

- Best mounting choice in most applications



STEEL TUBE

- For extra strength & use in harsh environments



3 PORTED HEAD

- For convenient air connection



SWITCHES

- Available in Reed and Triac
- 15ft. cable with flying leads; available with quick-disconnect couplers



SEALS OF VITON[®] MATERIAL **V**

- Long lasting seal option
- High temperature applications



EXTRA CABLE **XA XB**

- To remotely locate cable cylinder

MIL SPEC CABLES

- Field proven to provide millions of cycles of uninterrupted service
- Nylon jacketed aircraft cables manufactured under Mil Spec. MIL-W-83420D