

IMA Features



- 4 frame sizes with integrated servo motor
- Compact, lightweight design ideal for replacing pneumatic and hydraulic cylinders
- Forces up to 30.5 kN (6,850 lbf)
- Roller and ball screw options
- Connector and feedback options to match most servo drives
- IP65 standard; IP67 option
- Skewed winding provides superior force repeatability
- Low electrical time constant motors allows high frequency moves with increased dynamic performance
- Easy-to-use re-lubrication port maximizes service life