

RSA-HT Features



- 4 frame sizes with upgraded force/torque transmission components (bearings, couplers, belts, pulleys)
- General automation & hydraulic replacement applications
- Forces of up to 13,039 lbf (58,001 N)
- Stroke lengths up to 60 inches (1,524 mm)
- Roller and ball screw options
- Standard thrust rod anti-rotation feature
- IP67 option to protect against dust and water ingress
- Your Motor Here[®] compatible
- Flexible mounting options