




338 x 1 - 01 Series Disc Brake Hydraulically Actuated Caliper Part Number 3035-0000

**Disc Brake and/or Skid Control Systems
For: Competition • Automotive - Truck
• Industrial • Military • Aircraft**



SPECIFICATIONS

Weight: 12.0 Lbs.

Normal Maximum
Operating Pressure: 1350 PSI

Total Effective Piston Area: 8.91 Square Inches

Total Pressure Developed: 12,028 Lbs., @ 1350 PSI

Torque Developed: 6.53 x Pressure in PSI x
(Disc Radius — 1-5/8")


Bleeding: Caliper must be mounted at
3 or 9 O'Clock to bleed in position.

Disc: Caliper is supplied to fit discs .250
inches thick, or up to .62" thick using
3 supplied 1/8" thick spacers.

Lining: 2 linings, each 8.3 square inches,
5/16" usable thickness.

Mounting: Caliper is designed to mount in a fixed
position for use on a fixed disc.

Fluid Media: Automotive Brake Fluid.



WARNING!

Only use fluid taken from an unopened container or one which has been kept tightly closed. Brake fluid will absorb water from the atmosphere which will cause fluid boiling at much lower temperatures and will result in loss of brakes.

INSTALLATION SPECIFICATIONS:

1. Mounting Bracket: Mounting bracket may be placed under bolt heads or nuts, or may be used as a spacer. Minimum bracket material thickness is to be .25 inches.
2. Caliper, must be mounted at 3:00 or 9:00 o'clock to bleed properly. If mounted in a different position, caliper must be rotated to proper position, bled, then rotated back to mounting position. Bleed screws and adapter assemblies, and inlet port fittings, may be swapped from side to side of caliper to produce correct mounting position for bleed screws. Both bleed screws must always be on the same side of the caliper.
3. This caliper is designed for automotive type (D.O.T. 3) brake fluid only. Use of any other type can cause seal damage which could result in brake failure.



TOL-O-MATIC, INC.

3800 County Road 116, Hamel, MN 55340

<http://www.Tolomatic.com> • Email: Help@Tolomatic.com

Phone: (763) 478-8000 • Fax: (763) 478-8080 • Toll Free: 1-800-328-2174



Information furnished is believed to be accurate and reliable. However, Tol-O-Matic assumes no responsibility for its use or for any errors that may appear in this document. Tol-O-Matic reserves the right to change the design or operation of the equipment described herein and any associated motion products without notice. Information in this document is subject to change without notice.